

BNC Female to BNC Female Cable Tinned Aluminum RG405 Type .086 Coax in 24 Inch

The BNC female to BNC female 24 inch cable using Tinned Aluminum RG405 type .086 coax, part number FMCA2991-24, from Fairview Microwave is in-stock and ships same day. This Fairview BNC to BNC cable assembly has a female to female gender configuration with 50 ohm semi-rigid FM-SR086ALTN-STR coax. Fairview Microwave's semi-rigid RF cable assemblies are ideal for high performance applications and can be formed, using proper tooling, to the routing pattern required.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.



Configuration:

- BNC Female
- BNC Female
- FM-SR086ALTN-STR

Applications:

- General Purpose
- Laboratory Use

Mechanical Specifications

Cable Assembly

Length*	24 in [609.6 mm]
Weight	0.098 lbs [44.45 g]

Cable

Cable Type	FM-SR086ALTN-STR
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper Clad Steel, Silver
Dielectric Type	PTFE
Number of Shields	1
Outer Conductor Material and Plating	Tinned Aluminum
One Time Minimum Bend Radius	0.05 in [1.27 mm]

Connectors

Description	Connector 1	Connector 2
Type	BNC Female	BNC Female
Impedance	50 Ohms	50 Ohms
Body Material & Plating	Brass, Nickel	Brass, Nickel

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Fairview Microwave
301 Leora Ln., Suite 100
Lewisville, TX 75056
Tel: 1-800-715-4396 / (972) 649-6678
Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

How to Order

Part Number Configuration:

FMCA2991 - xx uu

cm = Centimeters

<blank> = Inches

Length

Example: FMCA2991-12 = 12 inches long cable
FMCA2991-100cm = 100 cm long cable

BNC Female to BNC Female Cable Tinned Aluminum RG405 Type .086 Coax in 24 Inch from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [BNC Female to BNC Female Cable Tinned Aluminum RG405 Type .086 Coax in 24 Inch FMCA2991-24](https://www.fairviewmicrowave.com/bnc-female-to-bnc-female-cable-tinned-aluminum-rg405-type-.086-coax-fmca2991-24)

URL: <https://www.fairviewmicrowave.com/bnc-female-to-bnc-female-cable-tinned-aluminum-rg405-type-.086-coax-fmca2991-24-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

		REVISIONS			
REV.		DESCRIPTION	DATE	APPROVED	
A		INITIAL RELEASE	8/4/2022	AGANWANI	

NOTES:
1. CABLES 36" AND UNDER HAVE 1 LABEL CENTERED.
CABLES OVER 36" HAVE 2 LABELS, ONE AT EACH END
6.0" FROM THE FRONT OF THE CONNECTOR.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT
ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

Fairview Microwave an INFINITE brand		UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS		THIRD-ANGLE PROJECTION 	
		TOLERANCES:		CABLE LENGTH (L) TOLERANCES:	
.X = ±.2 [.508]		FRACTIONS ± 1/32		L ≤ 12 [305] = +1 [25] / -0	
.XX = ±.02 [.51]		ANGLES ± 1°		12 [305] < L ≤ 60 [1524] = +2 [51] / -0	
.XXX = ±.005 [.13]				60 [1524] < L ≤ 120 [3048] = +4 [102] / -0	
				120 [3048] < L ≤ 300 [7620] = +6 [152] / -0	
				300 [7620] < L = +5%L / -0	
ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.					
SIZE A		CAGE CODE 3FKR5		DRAWN BY PSRINIVAS	
				ITEM NO. FMCA2991	
				REV A	

TITLE

BNC Female to BNC Female Cable Tinned Aluminum
RG405 Type .086 Coax in 24 Inch

SHEET 1 OF 1

SCALE N/A

T-Rev.D