

## BNC Female to BNC Female Cable Tinned Copper RG405 Type .086 Coax in 200 CM Length

The BNC female to BNC female 200 cm cable using Tinned Copper RG405 type .086 coax, part number FMCA3053-200CM, from Fairview Microwave is in-stock and ships same day. This Fairview BNC to BNC cable assembly has a female to female gender configuration with 50 ohm semi-rigid FM-SR086CUTN-STR coax. Fairview Microwave's semi-rigid RF cable assemblies are ideal for high performance applications and can be formed, using proper tooling, to the routing pattern required.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

### Mechanical Specifications

#### Cable Assembly

Length\* 78.74 in [200 cm]  
Weight 0.168 lbs [76.2 g]

#### Cable

Cable Type FM-SR086CUTN-STR  
Impedance 50 Ohms  
Inner Conductor Type Solid  
Inner Conductor Material and Plating Copper Clad Steel, Silver  
Dielectric Type PTFE  
Number of Shields 1  
Shield Layer 1 Tinned Copper

One Time Minimum Bend Radius 0.05 in [1.27 mm]

#### Connectors

Description	Connector 1	Connector 2
Type	BNC Female	BNC Female
Impedance	50 Ohms	50 Ohms
Body Material & Plating	Brass, Nickel	Brass, Nickel



### Configuration:

- BNC Female
- BNC Female
- FM-SR086CUTN-STR

### Applications:

- General Purpose
- Laboratory Use

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data


Notes:

Fairview Microwave  
301 Leora Ln., Suite 100  
Lewisville, TX 75056  
Tel: 1-800-715-4396 / (972) 649-6678  
Fax: (972) 649-6689  
[www.fairviewmicrowave.com](http://www.fairviewmicrowave.com)  
[sales@fairviewmicrowave.com](mailto:sales@fairviewmicrowave.com)

## How to Order

Part Number Configuration:

**FMCA3053 - xx uu**



Example: FMCA3053-12 = 12 inches long cable  
FMCA3053-100cm = 100 cm long cable


BNC Female to BNC Female Cable Tinned Copper RG405 Type .086 Coax in 200 CM Length from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [BNC Female to BNC Female Cable Tinned Copper RG405 Type .086 Coax in 200 CM Length FMCA3053-200CM](#)

URL: <https://www.fairviewmicrowave.com/bnc-female-to-bnc-female-cable-tinned-copper-rg405-type-.086-coax-fm-ca3053-200cm-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	08/04/22	AGANWANI



**NOTES:**

1. CABLES 36" AND UNDER HAVE 1 LABEL CENTERED.  
CABLES OVER 36" HAVE 2 LABELS, ONE AT EACH END  
6.0" FROM THE FRONT OF THE CONNECTOR.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

<p><b>Fairview Microwave</b> an INFINIT<sup>®</sup> brand</p>	UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [ ] ARE MILLIMETERS		THIRD-ANGLE PROJECTION <p>THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF FAIRVIEW MICROWAVE CORPORATION. ALL RIGHTS RESERVED.</p>
	TOLERANCES:	CABLE LENGTH (L) TOLERANCES:	
TITLE <b>BNC Female to BNC Female Cable Tinned Copper RG405 Type .086 Coax in 200 CM Length</b>	.X = ±.2 [ .508] FRACTIONS .XX = ±.02 [ .51] ± 1/32 .XXX = ±.005 [ .13] ANGLES ± 1°	L ≤ 12 [305] = +1 [25] / -0 12 [305] < L ≤ 60 [1524] = +2 [51] / -0 60 [1524] < L ≤ 120 [3048] = +4 [102] / -0 120 [3048] < L ≤ 300 [7620] = +6 [152] / -0 300 [7620] < L = +5%L / -0	SCALE N/A
ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.			REV A
SIZE A	CAGE CODE 3FKR5	DRAWN BY VTHANGARAJ	ITEM NO. FMCA3053

T-Rev.D