

## RA SHV Plug to SHV Jack Cable 75 Ohm RG-59 Black Coax in 60 Inch

The RA SHV plug to SHV jack 60 inch cable using 75 ohm RG-59 coax, part number FMCA3148-60, from Fairview Microwave is in-stock and ships same day. This Fairview SHV to SHV cable assembly has a plug to jack gender configuration with 75 ohm flexible RG59 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMCA3148-60 SHV plug to SHV jack cable assembly operates to 300 MHz. The right angle SHV interface on the RG59 cable allows for easier connections in tight spaces. Safety high voltage connectors are designed to allow signal transmission with high voltage ratings without safety risk for the operators. Both the pin and socket contacts are securely recessed inside the insulation to guard against potential electrical shock when live unmated connectors are handled.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

### Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		300	MHz
Velocity of Propagation		66		%
Capacitance		20.4 [66.93]		pF/ft [pF/m]
Operating Voltage (AC)			2,300	Vrms

### Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency		0.1	0.25	0.3		GHz
Insertion Loss (Max.)	0.49	0.6	0.62			dB

#### Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1 dB for the Jack connector and 0.2 dB for the Plug connector.

### Mechanical Specifications

#### Cable Assembly

Length\* 60 in [152.4 cm]  
 Weight 0.302 lbs [136.98 g]

#### Cable

Cable Type RG59  
 Impedance 75 Ohms  
 Inner Conductor Type Solid  
 Inner Conductor Material and Plating Copper Clad Steel  
 Dielectric Type PE  
 Number of Shields 1



### Configuration:

- SHV Plug Right Angle
- SHV Jack
- RG59

### Features:

- Max Frequency 300 MHz
- 66% Phase Velocity
- PVC (NC) Jacket
- Recessed contacts prevent shock hazards
- Dielectric withstanding of 5kV
- Shock, Moisture & Corrosion resistant

### Applications:

- General Purpose
- Laboratory Use
- Nuclear Instrumentation
- High Voltage Electrical Transmission
- Semiconductor Test

Fairview Microwave  
 301 Leora Ln., Suite 100  
 Lewisville, TX 75056  
 Tel: 1-800-715-4396 / (972) 649-6678  
 Fax: (972) 649-6689  
[www.fairviewmicrowave.com](http://www.fairviewmicrowave.com)  
[sales@fairviewmicrowave.com](mailto:sales@fairviewmicrowave.com)




RA SHV Plug to SHV Jack Cable 75 Ohm RG-59 Black Coax in 60 Inch from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [RA SHV Plug to SHV Jack Cable 75 Ohm RG-59 Black Coax in 60 Inch FMCA3148-60](#)

URL: <https://www.fairviewmicrowave.com/ra-shv-plug-to-shv-jack-cable-75-ohm-rg59-black-coax-in-60-inch-fmca3148-60-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.





RA SHV Plug to SHV Jack Cable 75 Ohm RG-59 Black Coax in 60 Inch