

BNC Plug Right Angle to SMP Plug Right Angle using RG316 Coax Cable in 24 Inches

FMCA9848-24




Configuration

- Connector 1: MCX Plug Right Angle
- Connector 2: SMP Plug Right Angle
- Cable Type: RG316

Features

- Max Frequency 3 GHz
- 69% Phase Velocity
- VSWR of 1.4:1



Applications

- General Purpose
- Laboratory Use
- Military
- Aerospace
- Wireless Communications
- General Purpose Test

Description

The RA MCX plug to RA SMP plug 24 inch cable using RG316, part number FMCA9848-24, from Fairview Microwave is in-stock and ships same day. This Fairview MCX to SMP cable assembly has a plug to plug gender configuration with 50 ohm RG316. The FMCA9848-24 MCX plug to SMP plug cable assembly operates to 3 GHz. The right angle MCX and right angle SMP interfaces on the RG316 cable allow for easier connections in tight spaces.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		3	GHz
VSWR			1.4:1	
Velocity of Propagation		69		%
Capacitance		29.4 [96.46]		pF/ft [pF/m]

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.1	0.25	0.5	1	3	GHz
Insertion Loss (Typ.)	0.62	0.72	0.88	1.16	1.56	dB

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.2 dB per connector

BNC Plug Right Angle to SMP Plug Right Angle using RG316 Coax Cable in 24 Inches

FMCA9848-24



Mechanical Specifications

Cable Assembly

Length	24 in [609.6 mm]
Width/Diameter	0.5 in [12.7 mm]
Weight	0.03 lbs [13.61 g]

Cable

Cable Type	RG316
Impedance	50 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper Clad Steel, Silver
Dielectric Type	PTFE

Connectors

Description	Connector 1	Connector 2
Type	MCX Plug Right Angle	SMP Plug Right Angle
Impedance	50 Ohms	50 Ohms
Configuration	Right Angle	Right Angle
Contact Material and Plating	Bronze, Gold over Copper	Beryllium Copper, Gold over Copper
Body Material and Plating	Bronze, Copper-Tin-Zinc Alloy	Bronze, Copper-Tin-Zinc Alloy

Environmental Specifications

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:
Values at 25°C, sea level.

BNC Plug Right Angle to SMP Plug Right Angle
using RG316 Coax Cable in 24 Inches



FMCA9848-24

Typical Performance Data

How to Order

Part Number Configuration:

FMCA9848

- xx

uu

Unit of Measure:

cm = Centimeters

<blank> = Inches

Length

Base Number

Example: FMCA9848-12 = 12 inches long cable
FMCA9848-100cm = 100 cm long cable

BNC Plug Right Angle to SMP Plug Right Angle using RG316 Coax Cable in 24 Inches from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [BNC Plug Right Angle to SMP Plug Right Angle using RG316 Coax Cable in 24 Inches FMCA9848-24](#)

URL: <https://www.fairviewmicrowave.com/non-magnetic-ra-mcx-plug-to-ra-smp-plug-cable-rg316-coax-in-24-inch-fm-ca9848-24-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

FMCA9848-24 CAD Drawing

BNC Plug Right Angle to SMP Plug Right Angle using RG316 Coax Cable in 24 Inches

