

RA SSMA Male to SSMA Female 4 Hole Flange Cable FM-P047 Coax



FMCA9981

Configuration

- Connector 1: SSMA Male Right Angle
- Connector 2: SSMA Female 4 Hole Flange
- Cable Type: FM-P047
- Coax Flex Type: Flexible

Features

- Shielding Effectivity > 90 dB
- 70% Phase Velocity
- Double Shielded
- FEP Jacket

Applications

- General Purpose
- Laboratory Use

Description

The RA SSMA male to SSMA female 4 hole flange cable using FM-P047 coax, part number FMCA9981, from Fairview Microwave is in-stock and ships same day. This Fairview SSMA to SSMA cable assembly has a male to female gender configuration with 50 ohm flexible FM-P047 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The right angle SSMA interface on the FM-P047 cable allows for easier connections in tight spaces. Our RF cable assembly with SSMA 4 hole flange interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications. The double shielding of this Fairview cable assembly provides excellent shielding effectiveness of better than 90 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Velocity of Propagation		70		%
RF Shielding	90			dB
Capacitance		29 [95.14]		pF/ft [pF/m]

Mechanical Specifications

Cable Assembly

Weight 0.016 lbs [7.26 g]

Cable

Cable Type FM-P047
Impedance 50 Ohms
Inner Conductor Type Solid

RA SSMA Male to SSMA Female 4 Hole Flange Cable FM-P047 Coax



FMCA9981

Inner Conductor Material and Plating	Copper, Silver
Dielectric Type	FEP
Number of Shields	2
Shield Layer 1	Silver Plated Copper Tape
Shield Layer 2	Silver Plated Copper Braid
Jacket Material	FEP, Blue
Jacket Diameter	0.056 in [1.42 mm]
One Time Minimum Bend Radius	0.2 in [5.08 mm]
Repeated Minimum Bend Radius	0.4 in [10.16 mm]

Connectors

Description	Connector 1	Connector 2
Type	SSMA Male Right Angle	SSMA Female 4 Hole Flange
Specification	MIL-C-39012	MIL-STD-348
Impedance	50 Ohms	50 Ohms
Configuration	Right Angle	Straight
Contact Material and Plating	Gold	Gold
Contact Plating Specification	MIL-G-45204	MIL-G-45204
Dielectric Type	Teflon	PTFE
Body Material and Plating	Brass, Gold	Stainless Steel, Gold
Body Plating Specification	MIL-G-45204	MIL-G-45204
Coupling Nut Material and Plating	Brass, Nickel	
Hex Size	1/4 in.	
Torque	3 in-lbs 0.34 Nm	

Environmental Specifications

Operating Range Temperature	-65 to +165 deg C
-----------------------------	-------------------

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

RA SSMA Male to SSMA Female 4 Hole Flange Cable FM-P047 Coax



FMCA9981

Typical Performance Data

How to Order

Part Number Configuration:

FMCA9981

- xx

uu

Unit of Measure:

cm = Centimeters

<blank> = Inches

Length

Base Number

Example: FMCA9981-12 = 12 inches long cable
FMCA9981-100cm = 100 cm long cable

RA SSMA Male to SSMA Female 4 Hole Flange Cable FM-P047 Coax from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [RA SSMA Male to SSMA Female 4 Hole Flange Cable FM-P047 Coax FMCA9981](#)

URL: <https://www.fairviewmicrowave.com/ra-ssma-male-to-ssma-female-4-hole-flange-cable-fm-p047-coax-fmca9981-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

FMCA9981 CAD Drawing
RA SSMA Male to SSMA Female 4 Hole Flange Cable FM-P047 Coax

