

TNC Male Connector Crimp/Solder Attachment for LMR-400, LMR-400-DB, LMR-400-UF, .400 inch Cable



FMCN5255

Configuration

- TNC Male Connector
- MIL-STD-348
- 50 Ohms
- Straight Body Geometry
- Connector Interface Types: LMR-400, LMR-400-DB, LMR-400-UF, .400 inch

Features

- Operating Frequency of 11 GHz Max.
- Silver Plated Brass Contact
- Contact plating according to ASTM-B700

Applications

- General Purpose Test
- Custom Cable Assemblies

Description

TNC Male Standard Connector Crimp/Solder Attachment for LMR-400, LMR-400-DB, LMR-400-UF and .400 inch Cable, part number FMCN5255, from Fairview Microwave is in-stock and ships same day. This TNC male connector operates up to a maximum frequency of 11 GHz.

Fairview's TNC male connector FMCN5255 datasheet specifications and outline drawing are shown in this PDF below. Our extensive offering of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. From providing an I/O for a board design to creating a custom cable assembly configuration, Fairview Microwave has a connector solution to meet your needs. Fairview Microwave also has the expertise to build your custom cable assemblies for you and ship them same-day.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		11	GHz
Operating Voltage (AC)			500	Vrms
Dielectric Withstanding Voltage (AC)			1,500	Vrms
Impedance		50		Ohms

Mechanical Specifications

Size

Length	1.68 in [42.67 mm]
Width	0.6 in [15.24 mm]
Height	0.6 in [15.24 mm]
Weight	0.067 lbs [30.39 g]

TNC Male Connector Crimp/Solder Attachment for LMR-400, LMR-400-DB, LMR-400-UF, .400 inch Cable

FMCN5255



Material Specifications

Description	Material	Plating
Contact	Brass	Silver ASTM-B700
Insulation	PTFE	
Body	Brass	Nickel ASTM-B689
Coupling Nut	Brass	Nickel ASTM-B689

Environmental Specifications

Temperature Operating Range	-65 to +165 deg C
--------------------------------	-------------------

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

TNC Male Connector Crimp/Solder Attachment for LMR-400, LMR-400-DB, LMR-400-UF, .400 inch Cable from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [TNC Male Connector Crimp/Solder Attachment for LMR-400, LMR-400-DB, LMR-400-UF, .400 inch Cable FMCN5255](#)

URL: <https://www.fairviewmicrowave.com/product/rf-connectors/tnc-male-lmr-400-lmr-400-db-lmr-400-uf-.400-connector-fmcn5255.html>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

FMCN5255 CAD Drawing

TNC Male Connector Crimp/Solder Attachment for LMR-400, LMR-400-DB, LMR-400-UF, .400 inch Cable

