

SMA F'S POWER DIVIDER 200-2500 MHZ

MP022500-2

SPECIFICATIONS

ELECTRICAL


FREQUENCY: 200-2500 MHZ
IMPEDANCE: 50 OHMS
VSWR: 1.5:1 MAX
INSERTION LOSS: 1.8 DB MAX
INPUT POWER(MAX) : 1 WATT
ISOLATION: 22 DB MIN

MECHANICAL


MATERIAL CONNECTORS: Ni PLATED BRASS
MATERIAL CONTACTS: Au PLATED BeCu
MATERIAL BODY: NICKEL PLATED ALUMINUM

OPERATING TEMPERATURE: -25°C TO +80°C

ROHS COMPLIANT



MEASUREMENTS BELOW ARE TYPICAL



ALL DIMENSIONS IN inches(MM) Typical

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

SMA F'S POWER DIVIDER 200-2500 MHZ

SIZE

A

CAGE CODE

3FKR5

DWG NO

MP022500-2

REV

--

SCALE

SHEET