

SMA POWER DIVIDER 8-WAY .8-2.5 GHZ

MP8209-8


SPECIFICATIONS

ELECTRICAL:


FREQUENCY: 8-2.5 GHZ
VSWR 1.4:1 MAX IN, 1.3 OUT
POWER CW: 10 WATTS CW
ISOLATION: 20 DB MIN
INSERTION LOSS: 10 DB (9+1)
AMPLITUDE BALANCE: 0.5DB MAX
IMPEDANCE: 50 OHMS

ENVIRONMENTAL:

TEMP: -25 C TO +55 C INDOOR
CONNECTORS: SMA-F, Au PLATED
HOUSING FINISH: PASS. ALUMINUM
ROHS COMPLIANT



MEASUREMENTS BELOW ARE TYPICAL



ALL DIMENSIONS IN inches(MM) Typical

FAIRVIEW MICROWAVE INC.			
ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM			
TITLE			
SMA POWER DIVIDER 8-WAY .8-2.5 GHZ			
SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	MP8209-8	A
SCALE		SHEET	