

# SMA FLEXABLE CABLES 26.5GHZ

## RF085F-0101-XX


### SPECIFICATIONS

CABLE ASSEMBLY:  
VSWR 1.4:1 MAX @ 26.5 GHZ

RAW CABLE: (HUBER SUHNER MULTIFLEX\_86 OR EQ)  
LOSS (EXCLUDING CONNECTORS)  
@ 1GHZ: 0.2 DB/FT  
@10GHZ: 0.8 DB/FT  
@18GHZ: 1.2 DB/FT  
@26.5GHZ: 1.344DB


SHIELD DIAMETER: .086"  
OVERALL DIA: .104"

CONNECTORS:  
BODY: PASSIVATED STAINLESS STEEL  
CONTACTS BeCu, Au PLATING MIL-G-45204  
INTERFACE: MIL-STD-348A



"XX" SPECIFIES LENGTH IN INCHES

### MEASUREMENTS BELOW ARE TYPICAL



## FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 [WWW.FAIRVIEWMICROWAVE.COM](http://WWW.FAIRVIEWMICROWAVE.COM)

TITLE

### SMA FLEXABLE CABLES 26.5GHZ

SIZE

**A**

CAGE CODE

3FKR5

DWG NO

**RF085F-0101-XX**

REV

**B**

SCALE

SHEET

ALL DIMENSIONS IN inches(MM) Typical