

SMA-M CONN. R ANGLE RG58 CRIMP / SOLDER

SC6058, SC6059

SPECIFICATIONS

ELECTRICAL:


FREQUENCY: 0-12 GHZ
VSWR 1.3:1 MAX
IMPEDANCE: 50 OHMS
OP. TEMP RANGE: -55C- +155C

MECHANICAL:

MATERIAL BODY: SC6058 Au PLATED S STEEL
MATERIAL BODY: SC6059 PASS. S STEEL
CENTER CONTACT: BRASS
CONTACT PLATING: GOLD MIL-G-45204
CAPTIVATED CONTACT
INSULATOR: TEFLON
INTERFACE: MIL-STD-348A

ROHS COMPLIANT

SC6058: Au PLATED
SC6059: PASSIVATED



FAIRVIEW MICROWAVE INC.				
ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM				
TITLE				
SMA-M CONN. R ANGLE RG58 CRIMP / SOLDER				
SIZE	CAGE CODE	DWG NO	REV	
A	3FKR5	SC6058, SC6059	--	
SCALE	SHEET			