

SMA-M CONN. R ANGLE RG55 CRIMP / SOLDER

SC6062

SPECIFICATIONS


ELECTRICAL:

FREQUENCY: 0-12 GHZ
VSWR 1.3:1 MAX
IMPEDANCE: 50 OHMS
OP. TEMP RANGE: -55C- +155C


MECHANICAL:

MATERIAL BODY: PASS. STAINLESS STEEL
CENTER CONTACT: BRASS
CONTACT PLATING: GOLD MIL-G-45204
CAPTIVATED CONTACT
INSULATOR: TEFLON
INTERFACE: MIL-STD-348A

ROHS COMPLIANT



SLEEVE



CAPTIVATED CONTACT

STRIPPING DIMENSIONS

				FAIRVIEW MICROWAVE INC.	
				ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	
				TITLE	
				SMA-M CONN. R ANGLE RG55 CRIMP / SOLDER	
		SIZE	CAGE CODE	DWG NO	REV
		A	3FKR5	SC6062	--
		SCALE			SHEET