

N Male (Plug) Connector Crimp/Solder Attachment for RG58, RG141, RG303, 0.195 inch, LMR®-195, LMR®-195-FR Cable



SC9109

Configuration

- N Male Connector
- MIL-STD-348
- 50 Ohms
- Straight Body Geometry
- Connector Interface Types: RG58, RG141, RG303, 0.195 inch, LMR®-195, LMR®-195-FR

Features

- Operating Frequency of 12 GHz Max.
- Good VSWR of 1.3:1
- Gold Plated Brass Contact
- Contact plating according to MIL-G-45204

Applications

- General Purpose Test
- Custom Cable Assemblies

Description

Type N Male Connector Crimp/Solder Attachment for RG58, RG141, RG303, 0.195 inch, LMR®-195 and LMR®-195-FR Cable, part number SC9109, from Fairview Microwave is in-stock and ships same day. This type N male connector operates up to a maximum frequency of 12 GHz and offers good VSWR of 1.3:1.

Fairview's type N male connector SC9109 datasheet specifications and outline drawing are shown in this PDF below. Our extensive offering of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. From providing an I/O for a board design to creating a custom cable assembly configuration, Fairview Microwave has a connector solution to meet your needs. Fairview Microwave also has the expertise to build your custom cable assemblies for you and ship them same-day.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		12	GHz
VSWR			1.3:1	
Impedance		50		Ohms

Mechanical Specifications

Size

Length	1.48 in [37.59 mm]
Width	0.78 in [19.81 mm]
Weight	0.068 lbs [30.84 g]

Material Specifications

Description	Material	Plating
Contact	Brass	Gold MIL-G-45204
Insulation	PTFE	
Body	Brass	Nickel QQ-N-290

N Male (Plug) Connector Crimp/Solder Attachment for RG58, RG141, RG303, 0.195 inch, LMR®-195, LMR®-195-FR Cable



SC9109

Environmental Specifications

Temperature

Operating Range

-55 to +155 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

N Male (Plug) Connector Crimp/Solder Attachment for RG58, RG141, RG303, 0.195 inch, LMR®-195, LMR®-195-FR Cable from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [N Male \(Plug\) Connector Crimp/Solder Attachment for RG58, RG141, RG303, 0.195 inch, LMR®-195, LMR®-195-FR Cable SC9109](#)

URL: <https://www.fairviewmicrowave.com/product/rf-connectors/n-male-rg58-rg141-rg303-0.195-lmr-195-lmr-195-fr-connector-sc9109.html>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

N Male (Plug) Connector Crimp/Solder Attachment for RG58, RG141, RG303, 0.195 inch, LMR®-195, LMR®-195-FR Cable

