

MCX-PLUG RG178 CRIMP

SC9418

SPECIFICATIONS

ELECTRICAL:

FREQUENCY: 0-6 GHZ
VSWR 1.25:1 MAX
IMPEDANCE: 50 OHMS
OP. TEMP RANGE: -55C to +125C





MECHANICAL:

MATERIAL BODY: BRASS AU PLATING 3μ"
CENTER CONTACT: Brass
CONTACT PLATING: 30 μ-in
INSULATOR: TEFLON

ROHS COMPLIANT

ASSEMBLY

TRIM CABLE AS SHOWN,
SLIDE CRIMP SLEEVE ON CABLE,
SOLDER ON CONTACT,
INSERT CABLE INTO BODY,
CRIMP



FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

MCX-PLUG RG178 CRIMP

SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	SC9418	
SCALE		SHEET	

ALL DIMENSIONS IN inches(MM) Typical