

SMA/MRA-SMA/M RG316 3 GHZ FLEXIBLE CABLES

SCA59316-XX

SPECIFICATIONS


CABLE ASSEMBLY:
VSWR: <1.2 TYPICAL @ 3GHZ

RAW CABLE: (RG316)
LOSS (EXCLUDING CONNECTORS)
@ 1GHZ: 0.26 DB/FT
@ 2GHZ: 0.38 DB/FT
@ 3GHZ: 0.47 DB/FT


OUTER DIAMETER: .098"

CONNECTORS:
SMA: NICKEL PLATED BRASS
INTERFACE: MIL-STD-348A
CONTACTS; Au PLATTING 30μ

TORQUE 5 IN-IBS



MEASUREMENTS BELOW ARE TYPICAL



ALL DIMENSIONS IN inches(MM) Typical

FAIRVIEW MICROWAVE

FAIRVIEW, TX WWW.FAIRVIEWMICROWAVE.COM

TITLE

SMA/MRA-SMA/M RG316 3 GHZ FLEXIBLE CABLES

SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	SCA59316-XX	--
SCALE	SHEET		