

SMA/M/RA-SMA/M/RA RG316 CABLES 3GHZ

SCB15036-XX

SPECIFICATIONS

CABLE ASSEMBLY:

VSWR: 1.3:1
IMPEDENCE: 50 OHMS
FREQUENCY: 0-3 GHZ
RECOMMENDED MAX FREQ: 3 GHZ


NOMINAL LOSS (EXCLUDING CONNECTORS)
@1 GHZ: 0.29 DB/FT
@6 GHZ: 0.69 DB/FT

MAX POWER: 170 WATTS
@1 GHZ: 140 WATTS


INTERFACE: MIL-STD-883
TORQUE: 5 IN-ILBS

OPERATING TEMP: -55 to +110°C

MIN BEND RADIUS: .50"



MEASUREMENTS BELOW ARE TYPICAL



ALL DIMENSIONS IN inches(MM) Typical

FAIRVIEW MICROWAVE

FAIRVIEW, TX WWW.FAIRVIEWMICROWAVE.COM

TITLE

SMA/M/RA-SMA/M/RA RG316 CABLES 3GHZ

SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	SCB15036-XX	A
SCALE	SHEET		