

SCB15785-XX

SPECIFICATIONS


CABLE ASSEMBLY:
VSWR: <1.2 TYPICAL @ 4GHZ

RAW CABLE:
LOSS (EXCLUDING CONNECTORS)
@ 1GHZ: 0.08 DB/FT
@ 3GHZ: 0.47 DB/FT
@ 6GHZ: 0.68 DB/FT


OVERALL DIAMETER: .195"

CONNECTORS:
SMA: NICKEL PLATED BRASS
CONTACTS: Au PLATING
INTERFACE: MIL-STD-348A

TORQUE WRENCH: 5 IN-IBS



MEASUREMENTS BELOW ARE TYPICAL



ALL DIMENSIONS IN inches(MM) Typical

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

SMA FLEXABLE CABLES LMR240 4GHZ

SIZE

A

CAGE CODE

3FKR5

DWG NO

SCB15785-XX

REV

--

SCALE

SHEET