

# SMA/M-RA-BNC/M FLEXIBLE CABLES 1GHZ RG58

## SCB15882-XX


### SPECIFICATIONS

CABLE ASSEMBLY:  
VSWR:1.2:1 @<1GHZ TYPICAL


RAW CABLE: RG58  
TYPICAL LOSS (EXCLUDING CONNECTORS)  
@1GHz: 0.15 DB/FT

CONNECTORS:  
BNC: BRASS  
SMA torque 5-in-lbs  
CONTACTS Au PLATING  
INTERFACE: MIL-STD-348A

OP TEMP: -55-110°C



MEASUREMENTS BELOW ARE TYPICAL



ALL DIMENSIONS IN inches(MM) Typical

**FAIRVIEW MICROWAVE INC.**

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

SMA/M-RA-BNC/M FLEXIBLE CABLES 1GHZ RG58

SIZE

**A**

CAGE CODE

3FKR5

DWG NO

**SCB15882-XX**

REV

--

SCALE

SHEET