

BNC/M/RA-N/M/RA FLEXIBLE CABLES 1GHZ RG58

SCB18031-XX


SPECIFICATIONS

CABLE ASSEMBLY:
VSWR:1.2:1 @ < 1GHZ TYPICAL


RAW CABLE: RG58
TYPICAL LOSS (EXCLUDING CONNECTORS)
@100MHZ: 0.05 DB/FT
@1GHZ: 0.15 DB/FT

CONNECTORS:
BNC: BRASS
CONTACTS Au PLATING
INTERFACE: MIL-STD-348A

OP TEMP: -55-110°C
ROHS COMPLIANT



MEASUREMENTS BELOW ARE TYPICAL



ALL DIMENSIONS IN inches(MM) Typical

FAIRVIEW MICROWAVE INC.			
ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM			
TITLE BNC/M/RA-N/M/RA FLEXIBLE CABLES 1GHZ RG58			
SIZE A	CAGE CODE 3FKR5	DWG NO SCB18031-XX	REV --
SCALE		SHEET	