

SMC/PLUG - SMC/JACK ADAPTER

SM2017

SPECIFICATIONS

ELECTRICAL

FREQUENCY: 0-10 GHZ

IMPEDANCE: 50 OHMS

VSWR: 1.2:1 MAX @ 10GHZ

MECHANICAL

MATERIAL BODY: NICKEL PLATED BRASS

FEMALE CONTACTS: BeCu


CONTACT PLATING: Au MIL-G-45204

INSULATOR: TEFLON

INTERFACE: MIL-STD-348A

ROHS COMPLIANT



OP TEMP -55°-125°C



.67"
(17.0)

SMC JACK

SMC PLUG



FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

SMC/PLG - SMC/JACK ADAPTER

ALL DIMENSIONS IN inches(MM) Typical	SIZE	CAGE CODE	DWG NO	REV
	A	3FKR5	SM2017	-
SCALE			SHEET	