


SPECIFICATIONS

ELECTRICAL

FREQUENCY: 0-1 GHZ
IMPEDANCE: 50 OHMS
VSWR: 1.2:1 MAX @ 1 GHZ

MECHANICAL

MATERIAL BODY: NICKEL PLATED
CENTER FEMALE CONTACT: BeCu
CENTER MALE CONTACT: BRASS
CONTACT PLATING: MIL-G-45204
INSULATOR: TEFLON
INTERFACE: MIL-STD-348A
ROHS COMPLIANT



S. M. ELECTRONICS L.L.C

FAIRVIEW, TX WWW.SMELECTRONICSLLC.COM

TITLE

BNC M/F ADAPTER 1 GHZ

SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	SM3450	A
SCALE			SHEET