**Fairview Microwave** 

# FM-SR141CU75-ST-BULK DATA SHEET

### 75 Ohm .141 Semi-Rigid Coax Cable with a Bare Copper Outer Conductor in Straight Sections

.141 diamater semi-rigid coaxial cable is the cable of choice for many RF and Microwave engineers. 0.141 cables sometimes referred to as RG402 based on the mil specification for semi-rigid cable of this diameter has a maximum operating frequency of 36 GHz. This form factor is widely used in the RF industry and many connector series and configurations are available for this cable. Because of the solid copper wall design the cable can be formed using proper tooling with a minimum inside bend radius of 1 inch.

#### **Electrical Specifications**

Description	Min	Т	ур	Max	Units
Frequency Range	DC			36	GHz
Impedance		7	75		0hms
DWV (AC)				3,500	Vrms

#### **Performance by Frequency Band**

Description	F1	F2	F3	F4	F5	Units
Frequency	1	10	20			GHz
Attenuation, Typ	12.5 41.01	51 167.32	78 255.91			dB/100ft dB/100m
Power In (CW), Max	280	60	39			Watts

### **Mechanical Specifications**

Min. Bend Radius (Installation)

1 in [25.4 mm]

### **Construction Specifications**

Description	Material and Plating	Diameter
Inner Conductor	Copper Clad Steel, Silver	0.02 in [0.51 mm]
Conductor Type	Solid	
Dielectric	PTFE	0.118 in [3 mm]
Outer Conductor	Copper, Bare	0 in [0 mm]
Jacket	Tan	[]

### **Environmental Specifications**

Temperature Operating Range

-55 to +200 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data Notes: Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com

## **Configuration:**

- Semi-Rigid Cable
- O Shield(s)

### **Features:**

- Silver Plated Copper Clad Steel center conductor
- PTFE dielectric material
- Bare Copper Outer Conductor
- Operating to 36 GHz
- Minimum inside bend radius of 1 inch
- ROHS compliant

## **Applications:**

- RF and Microwave Cable Assemblies to 36 GHz
- Preformed cable assemblies to insure fit and layout
- Test Equipment port jumpers

Fairview Microwave




# FM-SR141CU75-ST-BULK DATA SHEET

75 Ohm .141 Semi-Rigid Coax Cable with a Bare Copper Outer Conductor in Straight Sections from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: 75 Ohm .141 Semi-Rigid Coax Cable with a Bare Copper Outer Conductor in Straight Sections FM-SR141CU75-ST-BULK


URL: https://www.fairviewmicrowave.com/75-ohm-.141-semi-rigid-coax-cable-copper-fm-sr141cu75-st-bulk-p.aspx



Fairview Microwave







301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689