

5 dBi Rubber Duck Antenna 900-930 MHz RP-TNC Connector

The Fairview Microwave FM51RD1019 is an economical yet superior performance omnidirectional “rubber-duck” antenna designed for the 900 MHz ISM band. It features a RIGID Reverse Polarity TNC (RP-TNC) male connector, allowing superior weatherproofing for indoor and outdoor applications. It is a coaxial sleeve design with an omni-directional pattern. It is ideally suited for 900MHz ISM band applications as well as cellular and LPWAN applications.

The high performance rubber-duck FM51RD1019 from Fairview Microwave’ is a flexible antenna providing broad coverage and 5.0 dBi gain. Measuring 16.0 inches long, this 5.0 dBi antenna makes a great upgrade to OEM supplied antennas offering much larger coverage area and stronger signals. It is suitable as a replacement RF antenna for 900 MHz radios that are equipped with RP-TNC connectors.

In addition to shipping the same day, our rubber duck antennas are high-quality components backed by expert technical support and sales personnel. Contact our knowledgeable and friendly technical support and sales staff for your answers on antennas or other Fairview Microwave products.

Configuration

Design	Rubber Duck
Gain	5
Polarization	Vertical
Connector Type	TNC Male Reverse Polarity
Number of Ports	1

Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	900		930	MHz
Input VSWR			2.5:1	
Impedance		50		Ohms
Gain		5		dBi
Input Power			50	Watts

Mechanical Specifications

Radome Material	Plastic
Housing Plating/Color	Black
Size	
Length	16 in [406.4 mm]
Width	0.51 in [12.95 mm]
Height	0.51 in [12.95 mm]
Weight	1.164 lbs [527.98 g]

Environmental Specifications

Temperature	
Operating Range	-40 to +90 deg C



Features:

- Better performance than Most Stock AP Antennas
- Flexible “Rubber Duck” Antenna
- RP-TNC Plug Connector

Applications:

- 900 MHz Digital Spread Spectrum Radios
- 900 MHz ISM Band
- LPWAN, LoRA, IoT, M2M Applications
- 900 MHz Telemetry Products
- Cellular Band Applications

Fairview Microwave
301 Leora Ln., Suite 100
Lewisville, TX 75056
Tel: 1-800-715-4396 / (972) 649-6678
Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

5 dBi Rubber Duck Antenna 900-930 MHz RP-TNC Connector from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [5 dBi Rubber Duck Antenna 900-930 MHz RP-TNC Connector FM51RD1019](#)

URL: <https://www.fairviewmicrowave.com/single-antenna-900-930-mhz-5-dbi-gain-tnc-fm51rd1019-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

