

## N Male to N Male Cable RG-316 Coax

### Electrical Specifications

| Description             | Min | Typ         | Max    | Units        |
|-------------------------|-----|-------------|--------|--------------|
| Frequency Range         | DC  |             | 3      | GHz          |
| VSWR                    |     |             | 1.35:1 |              |
| Velocity of Propagation |     | 70          |        | %            |
| Capacitance             |     | 32 [104.99] |        | pF/ft [pF/m] |

### Mechanical Specifications

#### Cable Assembly

Weight 0.00618 lbs [2.8 g]

#### Cable

Cable Type RG-316  
 Impedance 50 Ohms  
 Inner Conductor Type Solid  
 Inner Conductor Material and Plating Copper, Silver  
 Dielectric Type PTFE  
 Number of Shields 1  
 Shield Layer 1 Silver Plated Copper Braid  
 Jacket Material FEP, Tan  
 Jacket Diameter 0.098 in [2.49 mm]

#### Connectors

| Description                     | Connector 1            | Connector 2            |
|---------------------------------|------------------------|------------------------|
| Type                            | N Male                 | N Male                 |
| Impedance                       | 50 Ohms                | 50 Ohms                |
| Configuration                   | Straight               | Straight               |
| Contact Material & Plating      | Beryllium Copper, Gold | Beryllium Copper, Gold |
| Dielectric Type                 | PTFE                   | PTFE                   |
| Coupling Nut Material & Plating |                        | Brass, Nickel          |
| Body Material & Plating         | Brass, Nickel          |                        |

### Environmental Specifications

#### Temperature

Operating Range -55 to +125 deg C

**Compliance Certifications** (visit [www.FairviewMicrowave.com](http://www.FairviewMicrowave.com) for current document)

### Plotted and Other Data

Notes:




### Configuration:

- N Male
- N Male
- RG-316

Fairview Microwave  
 1130 Junction Dr. #100  
 Allen, TX 75013  
 Tel: 1-800-715-4396 / (972) 649-6678  
 Fax: (972) 649-6689  
[www.fairviewmicrowave.com](http://www.fairviewmicrowave.com)  
[sales@fairviewmicrowave.com](mailto:sales@fairviewmicrowave.com)

## Typical Performance Data



## How to Order

Part Number Configuration:

**FMC0101315 - xx uu**

cm = Centimeters  
<blank> = Inches

Length


Example: FMC0101315-12 = 12 inches long cable  
FMC0101315-100cm = 100 cm long cable

N Male to N Male Cable RG-316 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [N Male to N Male Cable RG-316 Coax FMC0101315](#)

URL: <http://www.fairviewmicrowave.com/standard-n-male-n-male-cable-rg316-coax-fmc0101315-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



# FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

## NOTES:

1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES [mm].

|       |            |        |           |       |      |
|-------|------------|--------|-----------|-------|------|
| TITLE | DWG NO     |        | CAGE CODE |       |      |
|       | FMC0101315 |        | 3FKR5     |       |      |
|       | CAD FILE   | 022506 | SHEET     | SCALE | N/A  |
|       |            |        |           | SIZE  | A    |
|       |            |        |           |       | 5568 |

N Male to N Male Cable RG-316 Coax