

SMA Male to RA MMCX Plug Cable RG174 Coax with LF Solder

The SMA male to RA MMCX plug cable using RG174 coax, part number FMC0219174LF, from Fairview Microwave is in-stock and ships same day. This Fairview SMA to MMCX cable assembly has a male to plug gender configuration with 50 ohm flexible RG-174 coax. Fairview Microwave’s flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMC0219174LF SMA male to MMCX plug cable assembly operates to 500 MHz. The right angle MMCX interface on the RG-174 cable allows for easier connections in tight spaces.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		500	MHz
VSWR			1.35:1	
Velocity of Propagation		66		%
Capacitance		30.94 [101.51]		pF/ft [pF/m]


Mechanical Specifications

Cable Assembly

Length* 0 in [0 mm]

Cable

Cable Type RG-174
 Impedance 50 Ohms
 Inner Conductor Type Solid
 Inner Conductor Material and Plating Copper Clad Steel
 Dielectric Type PE
 Number of Shields 1
 Shield Layer 1 Tinned Copper Braid
 Jacket Material PVC, Black
 Jacket Diameter 0.102 in [2.59 mm]



Configuration:

- SMA Male
- MMCX Plug Right Angle
- RG-174

Features:

- Max Frequency 500 MHz
- 66% Phase Velocity
- PVC Jacket

Applications:

- General Purpose
- Laboratory Use

Fairview Microwave
 301 Leora Ln., Suite 100
 Lewisville, TX 75056
 Tel: 1-800-715-4396 / (972) 649-6678
 Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Connectors

Description	Connector 1	Connector 2
Type	SMA Male	MMCX Plug
Impedance	50 Ohms	50 Ohms
Contact Material & Plating	Brass, Gold	Brass, Gold
Contact Plating Spec.	50µ in. minimum	
Dielectric Type	PTFE	PTFE
Body Material & Plating	Brass, Nickel	Brass, Gold
Body Plating Spec.	100µ in. minimum	
Hex Size	5/16 inch	
Torque	4 in-lbs 0.45 Nm	

Environmental Specifications
Temperature

Operating Range -65 to +165 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

How to Order

Part Number Configuration: **FMC0219174LF - xx uu**

cm = Centimeters
<blank> = Inches

Length


Example: FMC0219174LF-12 = 12 inches long cable
FMC0219174LF-100cm = 100 cm long cable

SMA Male to RA MMCX Plug Cable RG174 Coax with LF Solder from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [SMA Male to RA MMCX Plug Cable RG174 Coax with LF Solder FMC0219174LF](#)

URL: <https://www.fairviewmicrowave.com/standard-sma-male-ra-mmcx-plug-cable-rg174-coax-fmc0219174lf-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM		NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].			
TITLE SMA Male to RA MMCX Plug Cable RG174 Coax with LF Solder		DWG NO FMC0219174LF		CAGE CODE 3FKR5	
CAD FILE	101614	SHEET	SCALE	N/A	SIZE A 5568