

# FMC0713315 DATA SHEET

## MCX Plug to SMA Female Cable RG-316 Coax

## **Electrical Specifications**

Description	Min	Тур	Max	Units			
Frequency Range	DC		3	GHz			
VSWR		1.35:1					
Velocity of Propagation		70					
Capacitance	3	32 [104.99]					

## **Mechanical Specifications**

**Cable Assembly** 

Weight 0.00794 lbs [3.6 g]

Cable

Cable Type
Impedance
Inner Conductor Type
Inner Conductor Material and Plating
Dielectric Type
RG-316
50 Ohms
Stranded
Copper, Silver
PTFE

Dielectric Type
Number of Shields

Shield Layer 1 Silver Plated Copper Braid Jacket Material FEP, Tan
Jacket Diameter 0.098 in [2.49 mm]

#### **Connectors**

Description	Connector 1	Connector 2		
Туре	MCX Plug	SMA Female		
Polarity	Standard	Standard		
Impedance	50 Ohms	50 Ohms		
Contact Material & Plating	Brass, Gold	Beryllium Copper, Gold		
Contact Plating Spec.	30µ" Min	50µ in. minimum		
Dielectric Type	PTFE	PTFE		
Hex Size		1/4 inch		
Body Material & Plating	Brass, Gold	Brass, Gold		
Body Plating Spec.	3µ" Minimum	3μ in. minimum		

# **Environmental Specifications Temperature**

remperature

Operating Range -65 to +165 deg C

**Compliance Certifications** (see product page for current document)

#### **Plotted and Other Data**

Notes:



## **Configuration:**

- MCX Plug
- SMA Female
- RG-316

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013


Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





### **Typical Performance Data**



MCX Plug to SMA Female Cable RG-316 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: MCX Plug to SMA Female Cable RG-316 Coax FMC0713315


URL: https://www.fairviewmicrowave.com/mcx-male-sma-female-cable-rg316-coax-fmc0713315-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

1130 Junction Dr. #100 Allen, TX 75013 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689







FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES:  1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.  2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.  3. DIMENSIONS ARE IN INCHES [mm].					
MCX Plug to SMA Female Cable RG-316 Coax	DWG NO FMC0713315			CAGE CODE 3FKR5		
	CAD FILE 102114	SHEET	SCALE	E N/A	SIZE A	5568