



BNC/M-SMB/P/RA FLEXIBLE CABLES 3GHZ RG316

FMC0826315-XX

SPECIFICATIONS

CABLE ASSEMBLY:

VSWR: 1.4 dB MAX @ 3GHZ

RAW CABLE: RG316

TYPICAL LOSS (EXCLUDING CONNECTORS)

@1GHZ: 0.26 DB/FT

@2GHZ: 0.38 DB/FT

@3GHZ: 0.47 DB/FT

OUTER SHIELD DIAMETER: .098"

CONNECTORS:

BNC:

MATERIAL BODY: Ni PLATED BRASS

CETNER CONTACT: BRASS

CONTACT PLATING: Au 30μ"

INSULATOR: TELFON

SMP PLUG RA:

MATERIAL BODY: BRASS

CONTACTS: BeCu


CONTACT PLATING: Au 30μ"

INSULATOR: TELFON


INTERFACE: MIL-STD-348A

OP TEMP: -55°C to +105°C

MEASUREMENTS BELOW ARE TYPICAL




PROTECTIVE HEAT SHRINK



BNC-M

SMB/PLUG RA



ALL DIMENSIONS IN inches(mm) Typical

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

BNC/M-SMB/P/RA FLEXIBLE CABLES 3GHZ RG316

SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	FMC0826315-XX	--
SCALE		SHEET	

