

SMB Plug (Male) to SMC Plug (Male) Cable M17/113-RG316 Coax Up To 3 GHz, 1.35 VSWR

The SMB plug to SMC plug cable using M17/113-RG316 coax, part number FMC1618316LF, from Fairview Microwave is in-stock and ships same day. This Fairview SMB to SMC cable assembly has a plug to plug gender configuration with 50 ohm flexible M17/113-RG316 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMC1618316LF SMB plug to SMC plug cable assembly operates to 3 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Min	Tvp		Max	ι	Units	
Frequency Range	DC	-	7 P	3		GHz	
VSWR				1.35:1		-	
Velocity of Propagation		7	'0			%	
Capacitance		32 [1	04.99		pF/f	t [pF/m]	

Mechanical Specifications

Cable Assembly Length*

Cable Type Impedance Inner Conductor Type Inner Conductor Material and Plating Dielectric Type Number of Shields Shield Layer 1 Jacket Material Jacket Diameter 0 in [0 mm]

M17/113-RG316 50 Ohms Solid Copper, Silver PTFE 1 Silver Plated Copper Braid FEP, Black 0.098 in [2.49 mm]





Configuration:

- SMB Plug
- SMC Plug
- M17/113-RG316

Features:

- Max Frequency 3 GHz
- 70% Phase Velocity
- FEP Jacket

Applications:

- General Purpose
- Laboratory Use

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com Fairview Microwave

an INFINIT[®] brand



Connectors

Description	Connector 1		Connector 2					
Туре	SMB Plu	SMB Plug		SMC Plug				
Impedance	50 Ohm	50 Ohms		50 Ohms				
Contact Material & Plating	Beryllium Copp	Beryllium Copper, Gold		Beryllium Copper, Gold				
Contact Plating Spec.	30µ in. minir	mum	50µ in. minimum					
Dielectric Type	PTFE		PTFE					
Body Material & Plating	Brass, Go	old	Brass, Gold					
Body Plating Spec.	3µ in. minin	num	3µ in. minimum					
Hex Size			1/4 ii	nch				
Temperature Operating Range ompliance Certificati lotted and Other Dat Notes:			-165 deg C urrent docum	nent)				
ow to Order								
Part Number Configura	tion:	FMC16:	18316LF	- xx	uu 		•	<blan< td=""></blan<>
							L	Lengt
	.6LF-12 = 12 inches .6LF-100cm = 100 c							

SMB Plug (Male) to SMC Plug (Male) Cable M17/113-RG316 Coax Up To 3 GHz, 1.35 VSWR from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: SMB Plug (Male) to SMC Plug (Male) Cable M17/113-RG316 Coax Up To 3 GHz, 1.35 VSWR FMC1618316LF


URL: https://www.fairviewmicrowave.com/standard-smb-plug-smc-plug-cable-rg316-coax-fmc1618316lf-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689







FAIRVIEW MICROWAVE INC.	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].					
™ MB Plug (Male) to SMC Plug (Male) Cable M17/113-	DWG NO	CAGE	CAGE CODE 3FKR5			
RG316 Čoàx Up To 3 GHz, 1.35 VSŴR	CAD FILE 103114	SHEET	SCALE N/A	SIZE A	5568	

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689