



MCX/M/RA-MCX/M/RA FLEXIBLE CABLES 3GHZ RG316

FMC1717315-XX

SPECIFICATIONS


CABLE ASSEMBLY:
VSWR: 1.2 dB MAX @ 3GHZ

RAW CABLE: RG316
TYPICAL LOSS (EXCLUDING CONNECTORS)
@1GHZ: 0.26 DB/FT
@2GHZ: 0.38 DB/FT
@3GHZ: 0.47 DB/FT


OUTER SHIELD DIAMETER: .098"

CONNECTORS:
MCX/RA:
MATERIAL BODY: BRASS
CENTER CONTACT: BRASS
CONTACT PLATING: 30μ"
CAPTIVATED CONTACT
INSULATOR: TEFLON

OP TEMP: -55°C to +105°C



MEASUREMENTS BELOW ARE TYPICAL



ALL DIMENSIONS IN inches(mm) Typical

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE
MCX/M/RA-MCX/M/RA FLEXIBLE CABLES 3GHZ RG316

SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	FMC1717315-XX	--

SCALE SHEET

