

## RA MMCX Plug to RA MMCX Plug Cable RG316 Coax

### Electrical Specifications

Frequency Range	DC to 3 GHz
Impedance	50 Ohms
Velocity of Propagation	70 %

### Mechanical Specifications

#### Temperature

Temperature Operating Range	-55 to +125 deg C
-----------------------------	-------------------

#### Size

Cable Color	Black
-------------	-------

#### Cable

Description	Cable
Cable Type	RG-316
Inner Conductor Type	Solid
Cable Inner Conductor	Copper, Silver
No of Shields	1
Dielectric Type	PTFE
Jacket Material	FEP
Jacket Diameter	0.098 in [2.49 mm]

#### Connectors

Description	Connector 1	Connector 2
Type	MMCX Plug Right Angle	MMCX Plug Right Angle
Configuration	Right Angle	Right Angle
Inner Conductor Material & Plating	Brass, Gold	Brass, Gold
Body Material & Plating	Brass, Gold	Brass, Gold
Dielectric Type	Teflon	Teflon

### Compliance Certifications (visit [www.FairviewMicrowave.com](http://www.FairviewMicrowave.com) for current document)

#### Notes:

- Values at +25 °C, sea level



### Configuration:

- MMCX Plug Right Angle
- MMCX Plug Right Angle
- RG-316

Fairview Microwave  
1130 Junction Dr. #100  
Allen, TX 75013  
Tel: 1-800-715-4396 / (972) 649-6678  
Fax: (972) 649-6689  
[www.fairviewmicrowave.com](http://www.fairviewmicrowave.com)  
[sales@fairviewmicrowave.com](mailto:sales@fairviewmicrowave.com)

### Typical Performance Data



### How to Order

Part Number Configuration:

**FMC1919315 - xx uu**

cm = Centimeters  
<blank> = Inches  
Length


Example: FMC1919315-12 = 12 inches long cable  
FMC1919315-100cm = 100 cm long cable

RA MMCX Plug to RA MMCX Plug Cable RG316 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [RA MMCX Plug to RA MMCX Plug Cable RG316 Coax FMC1919315-XX](http://www.fairviewmicrowave.com/ra-mmcx-male-ra-mmcx-male-cable-rg316-coax-fmc1919315-xx)

URL: <http://www.fairviewmicrowave.com/ra-mmcx-male-ra-mmcx-male-cable-rg316-coax-fmc1919315-xx-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



<b>FAIRVIEW MICROWAVE INC.</b> ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM		NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].			
TITLE RA MMCX Plug to RA MMCX Plug Cable RG316 Coax		DWG NO FMC1919315-XX		CAGE CODE 3FKR5	
CAD FILE	103114	SHEET	SCALE	N/A	SIZE A 5568