

2.4mm Female Connector Field Replaceable Attachment 2 Hole Flange with EMI gasket, accepts 0.23mm (.009inch) pin



FMCN1801

Configuration

- 2.4mm Female Connector
- 50 Ohms
- Straight Body Geometry
- Connector Interface Types: with EMI gasket, accepts 0.23mm (.009inch) pin
- 2 Hole Flange

Features

- Operating Frequency of 50 GHz Max.
- Excellent VSWR of 1.2:1
- Gold Plated Beryllium Copper Contact

Applications

- General Purpose Test
- Rack and Panel Mount Applications

Description

2.4mm Female 2 hole Flange Mount Standard 2 hole Flange Mount Connector Field Replaceable Attachment for with EMI gasket and accepts 0.23mm (.009inch) pin Cable, part number FMCN1801, from Fairview Microwave is in-stock and ships same day. This 2.4mm female connector operates up to a maximum frequency of 50 GHz and offers excellent VSWR of 1.2:1. Fairview's FMCN1801 2 hole flange 2.4mm connector enables designers to make external connections on product enclosures, and can be used in a variety of other rack mount and panel mount applications. Fairview's field replaceable connector is easy to install or replace in the field.

Fairview's 2.4mm female 2 hole flange connector FMCN1801 datasheet specifications and outline drawing are shown in this PDF below. Our extensive offering of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. From providing an I/O for a board design to creating a custom cable assembly configuration, Fairview Microwave has a connector solution to meet your needs. Fairview Microwave also has the expertise to build your custom cable assemblies for you and ship them same-day.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		50	GHz
VSWR			1.2:1	
Impedance		50		Ohms

Mechanical Specifications

Size

Length	0.427 in [10.85 mm]
Width	0.224 in [5.69 mm]
Height	0.625 in [15.88 mm]
Weight	0.1 lbs [45.36 g]

2.4mm Female Connector Field Replaceable Attachment 2 Hole Flange with EMI gasket, accepts 0.23mm (.009inch) pin



FMCN1801

Material Specifications

Description	Material	Plating
Contact	Beryllium Copper	Gold
Contact Spring	Passivated Stainless Steel	
Insulation	PEI	
Body	Passivated Stainless Steel	
Gasket	Conductive Silicone Elastomer	

Environmental Specifications

Temperature	
Operating Range	-40 to +150 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

2.4mm Female Connector Field Replaceable Attachment 2 Hole Flange with EMI gasket, accepts 0.23mm (.009inch) pin from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [2.4mm Female Connector Field Replaceable Attachment 2 Hole Flange with EMI gasket, accepts 0.23mm \(.009inch\) pin FMCN1801](#)

URL: <https://www.fairviewmicrowave.com/24mm-female-with-emi-gasket-accepts-03mm-012inch-pin-connector-fmcn1801-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

2.4mm Female Connector Field Replaceable Attachment 2 Hole Flange with EMI gasket, accepts 0.23mm (.009inch) pin

