

Coax Cable Stripper, 1/4 inch length for RG59, RG6, RG7, RG11

Configuration

Tool Type	Coax Cable Stripper
Cable Type	RG59, RG6, RG7, RG11

Mechanical Specifications

Size

Length	7.28 in [184.91 mm]
Width	4.76 in [121 mm]
Height	1.18 in [29.97 mm]
Weight	0.058 lbs [26.31 g]

Compliance Certifications (see [product page](#) for current document)

Notes:

- Values at 25 °C, sea level

Coax Cable Stripper, 1/4 inch length for RG59, RG6, RG7, RG11 from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [Coax Cable Stripper, 1/4 inch length for RG59, RG6, RG7, RG11 FMTL5215](#)

URL: <https://www.fairviewmicrowave.com/coax-cable-stripper-rg59-rg6-rg7-rg11-fmtl5215-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



Features:

- Stripper for 1/4" (6mm) length
- Strips coaxial cables RG59, RG6, RG7, RG11
- Compact size fits in your pocket and easy storage

Fairview Microwave
301 Leora Ln., Suite 100
Lewisville, TX 75056
Tel: 1-800-715-4396 / (972) 649-6678
Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	03/23/2023	HBAKKE	AGANWANI


FUNCTION:

- STRIPPING COAXIAL CABLE RG59, RG6, RG7/11.

FOR STRIPPING RG CABLE:

STRIPPING LENGTH (D):

2 BLADES MODE




D= 1/4"

FOR STRIPPING RG CABLE:

RG59/6/7/11 COAXIAL CABLE

FOR COAX. CABLE STRIPPER



BRAID FOLDING DOWN

<p>Fairview Microwave® an INFINITE® brand</p> <p>Website: www.FairviewMicrowave.com Phone: 1.800.715.4396 1.972.649.6678</p>	<p>UNLESS OTHERWISE SPECIFIED, LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS</p> <p>TOLERANCES:</p> <table style="font-size: small;"> <tr> <td>.X ± .2</td> <td>[.5]</td> <td>FRACTIONS</td> </tr> <tr> <td>.XX ± .02</td> <td>[.1]</td> <td>± .132</td> </tr> <tr> <td>.XXX ± .005</td> <td>[.13]</td> <td>ANGLES ± 1°</td> </tr> </table> <p>CABLE LENGTH TOLERANCES:</p> <table style="font-size: small;"> <tr> <td>≤ 12 [305]</td> <td>± .01 [253] / -0</td> </tr> <tr> <td>> 12 [305] ≤ 60 [1524]</td> <td>± .02 [51] / -0</td> </tr> <tr> <td>> 60 [1524] ≤ 120 [3048]</td> <td>± .03 [762] / -0</td> </tr> <tr> <td>> 120 [3048] ≤ 300 [7620]</td> <td>± .04 [1016] / -0</td> </tr> <tr> <td>> 300 [7620]</td> <td>± .05 [1270] / -0</td> </tr> </table> <p>ALL DIMENSIONS ARE FOR REFERENCE ONLY AND SUBJECT TO CHANGE WITHOUT NOTICE</p>	.X ± .2	[.5]	FRACTIONS	.XX ± .02	[.1]	± .132	.XXX ± .005	[.13]	ANGLES ± 1°	≤ 12 [305]	± .01 [253] / -0	> 12 [305] ≤ 60 [1524]	± .02 [51] / -0	> 60 [1524] ≤ 120 [3048]	± .03 [762] / -0	> 120 [3048] ≤ 300 [7620]	± .04 [1016] / -0	> 300 [7620]	± .05 [1270] / -0	<p>INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5</p> <p>SCALE: NONE</p> <p>SHEET: 1 OF 1</p> <p>DESCRIPTION: Tool, RG59/6/7/11 2-Blade, Ring Design</p>
.X ± .2	[.5]	FRACTIONS																			
.XX ± .02	[.1]	± .132																			
.XXX ± .005	[.13]	ANGLES ± 1°																			
≤ 12 [305]	± .01 [253] / -0																				
> 12 [305] ≤ 60 [1524]	± .02 [51] / -0																				
> 60 [1524] ≤ 120 [3048]	± .03 [762] / -0																				
> 120 [3048] ≤ 300 [7620]	± .04 [1016] / -0																				
> 300 [7620]	± .05 [1270] / -0																				

SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
A	3FKR5	HBAKKE	FMTL5215	A