

# FMWCP1080-20 DATA SHEET

# 20 dB WR-15 Waveguide Broadwall Coupler with UG-385/U Round Cover Flange and E-Plane Coupled Port from 50 GHz to 75 GHz in Brass Copper

The FMWCP1080-20 is a millimeter-wave directional waveguide coupler that operates in the frequency range of 50 to 75 GHz (V Band). This V band component offers a nominal coupling level of 20 dB, mean coupling accuracy of +/- 1, coupling flatness of 1.5 dB, and has a maximum VSWR level of 1.1:1. The design is made of gold brass copper and incorporates a multi-hole configuration that results in typical directivity of 40 dB. Common applications for this millimeter wave component involve test setups where power reflection measurements are required that might involve power sampling and frequency monitoring with minimal signal loss to the main transmission path. This E plane coupler uses integrated WR-15 waveguide ports with UG 385/U flanges. Fairview offers a complete family of waveguide millimeter wave directional couplers that are in-stock for same day shipment.

### **Electrical Specifications**

Description	Min	Тур	Max	Units
Frequency Range	50		75	GHz
Coupler				
Nominal Coupling Lev	el	20		dB
Coupling Accuracy			±1	dB
Directivity		40		dB
Insertion Loss			1	dB
Main Line VSWR			1.1:1	
Secondary Line VSW	R		1.15:1	
Coupling Flatness			±1.5	dB



#### **Features:**

- 20 dB Nominal Coupling Level
- E-Plane Waveguide Coupler
- 50 GHz to 75 GHz Frequency Range
- Body and Flanges made of Brass Copper
- Gold Waveguide
- 1.1:1 VSWR

## **Applications:**

- Test Benches
- Radar
- Satellite
- · Microwave Radio
- Attenuation Measurements
- Power Measurements
- Source Leveling

#### **Mechanical Specifications**

Size

 Length
 6 in [152.4 mm]

 Width
 0.75 in [19.05 mm]

 Height
 1.375 in [34.93 mm]

 Weight
 0.31 lbs [140.61 g]

**Interface** 

Waveguide Size

Flange Type

Flange Designation

Flange Material and Plating

Coupler Body Material and Plating

WR-15

Round Cover

UG-385/U

Brass Copper, Gold

Brass Copper, Gold

**Environmental Specifications** 

**Compliance Certifications** (see product page for current document)

**Plotted and Other Data** 

Notes:

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689

www.fairviewmicrowave.com sales@fairviewmicrowave.com





20 dB WR-15 Waveguide Broadwall Coupler with UG-385/U Round Cover Flange and E-Plane Coupled Port from 50 GHz to 75 GHz in Brass Copper from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: 20 dB WR-15 Waveguide Broadwall Coupler with UG-385/U Round Cover Flange and E-Plane Coupled Port from 50 GHz to 75 GHz in Brass Copper FMWCP1080-20

URL: https://www.fairviewmicrowave.com/20db-wr15-waveguide-broadwall-coupler-ug385-round-e-75ghz-fmwcp1080-20-p.aspx







