

M39012/56—SMA Right Angle Plug




Figure 1




Figure 2
(No lockwire holes)

| M39012 P/N | Category | Cable Group | Figure | Dimensions | | Plating | | Assembly Procedure/ Trim Code |
|----------------|----------|-------------|--------|------------|-----|---------------------|----------|----------------------------------|
| | | | | A | B | Body | Contact | |
| M39012/56-3006 | A | I | 1 | .68 | .55 | Gold ⁽²⁾ | Gold (C) | L / 06 |
| M39012/56-3007 | A | II | 1 | .68 | .55 | Gold ⁽²⁾ | Gold (C) | L / 06 |
| M39012/56-3008 | A | IV | 1 | .76 | .63 | Gold ⁽²⁾ | Gold (C) | L / 01 |
| M39012/56-3009 | A | VI | 1 | .76 | .63 | Gold ⁽²⁾ | Gold (C) | L / 01 |
| M39012/56-3025 | C | I | 1 | .68 | .55 | Passivated | Gold (C) | L / 06 |
| M39012/56-3026 | C | IIA | 1 | .74 | .61 | Passivated | Gold (C) | L / 06 |
| M39012/56-3027 | C | IV | 1 | .68 | .55 | Passivated | Gold (C) | L / 06 |
| M39012/56-3028 | C | VIB | 1 | .69 | .56 | Passivated | Gold (C) | L / 06 |
| M39012/56-3029 | C | VIA | 1 | .71 | .58 | Passivated | Gold (C) | L / 06 |
| M39012/56-3030 | A | III | 1 | .68 | .55 | Gold ⁽²⁾ | Gold (C) | L / 06 |
| M39012/56-3106 | A | I | 2 | .68 | .55 | Gold ⁽²⁾ | Gold (C) | L / 06 |
| M39012/56-3107 | A | II | 2 | .68 | .55 | Gold ⁽²⁾ | Gold (C) | L / 06 |
| M39012/56-3108 | A | IV | 2 | .76 | .63 | Gold ⁽²⁾ | Gold (C) | L / 01 |
| M39012/56-3109 | A | VI | 2 | .76 | .63 | Gold ⁽²⁾ | Gold (C) | L / 01 |
| M39012/56-3125 | C | I | 2 | .68 | .55 | Passivated | Gold (C) | L / 06 |
| M39012/56-3126 | C | IIA | 2 | .74 | .61 | Passivated | Gold (C) | L / 06 |
| M39012/56-3127 | C | IV | 2 | .68 | .55 | Passivated | Gold (C) | L / 06 |
| M39012/56-3128 | C | VIB | 2 | .69 | .56 | Passivated | Gold (C) | L / 06 |
| M39012/56-3129 | C | VIA | 2 | .71 | .58 | Passivated | Gold (C) | L / 06 |
| M39012/56-3130 | A | III | 2 | .68 | .55 | Gold ⁽²⁾ | Gold (C) | L / 06 |

(1) (2) See page 10 for notes.

M39012/57—SMA Straight Jack




Figure 1




Figure 2

| M39012 P/N | Category | Cable Group | Figure | Dimensions | | Plating | | Assembly Procedure/ Trim Code |
|----------------|----------|-------------|--------|------------|-----|---------------------|----------|----------------------------------|
| | | | | A | B | Body | Contact | |
| M39012/57-3006 | A | I | 1 | .87 | .63 | Gold ⁽²⁾ | Gold (C) | M / 01 |
| M39012/57-3007 | A | II | 1 | .87 | .63 | Gold ⁽²⁾ | Gold (C) | M / 01 |
| M39012/57-3008 | A | IV | 2 | .90 | .53 | Gold | Gold (C) | K / 12 |
| M39012/57-3009 | A | VI | 2 | .90 | .53 | Gold | Gold (C) | K / 12 |
| M39012/57-3025 | C | I | 1 | .87 | .63 | Passivated | Gold (C) | M / 01 |
| M39012/57-3026 | C | IIA | 1 | .93 | .63 | Passivated | Gold (C) | M / 01 |
| M39012/57-3027 | C | IV | 2 | .91 | .53 | Passivated | Gold (C) | K / 12 |
| M39012/57-3028 | C | VIB | 2 | .91 | .53 | Passivated | Gold (C) | K / 12 |
| M39012/57-3029 | C | VIA | 2 | .93 | .53 | Passivated | Gold (C) | K / 12 |
| M39012/57-3030 | A | III | 1 | .87 | .63 | Gold ⁽²⁾ | Gold (C) | M / 01 |

(1) (2) See page 12 for notes.

See page 2 for cable groups and category definitions. • Assembly procedures start on page 20. • (C) indicates captive contact.