

MMCX ATTENUATOR PLUG/JACK

SA3056-XX

SPECIFICATIONS

ELECTRICAL


FREQUENCY: 0-6 GHZ
 IMPEDANCE: 50 OHMS
 VSWR: 1.20:1 MAX
 POWER: 2 WATTS AVERAGE
 ATTENUATION ACCURACY:
 +/- 0.20 dB 3 GHZ

MECHANICAL


MATERIALS BODY: BRASS NI PLATING
 MATERIALS CONTACTS BeCu
 CONTACT PLATING Au PER MIL-G-45204
 INTERFACE: MIL-STD-348A
 INSULATOR: TEFLON

OP TEMP -55° TO +150° C

ROHS COMPLIANT



MEASUREMENTS BELOW ARE TYPICAL



ALL DIMENSIONS IN inches(mm) Typical

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

MMCX ATTENUATOR PLUG/JACK

SIZE

A

CAGE CODE

3FKR5

DWG NO

SA3056-XX

REV

A

SCALE

SHEET