

BNC-F BULKHEAD RG316 RG174 GRIP

SC6011

SPECIFICATIONS

ELECTRICAL:


FREQUENCY: 0-11 GHZ
 VSWR 1.3:1 MAX
 IMPEDANCE: 50 OHMS

MECHANICAL:



MATERIAL BODY: NICKLE PLATED BRASS
 CENTER CONTACT: BeCu
 CONTACT PLATING: Si QQ-S-365
 CAPTIVATED CONTACT
 INSULATOR: TEFLON
 INTERFACE: MIL-STD-348B
 ROHS COMPLIANT
 OP. TEMP RANGE: -55°C- +155°C

ASSEMBLY INSTRUCTIONS:


SLIDE BACKNUT ONTO CABLE
 TRIM CABLE AS SHOWN
 SLIT CABLE, 2 PLACES AS SHOWN, 180° APART
 SLIDE PIN ASSEMBLY UNDER BRAID
 SOLDER PIN ASSEMBLY TO CENTER CONDUCTOR
 INSERT ASSEMBLY INTO BODY
 TIGHTEN BY HOLDING NUT, TURNING BODY



BNC-F



STRIPPING DIMENSIONS



RECOMMENDED
 PANEL CUTOUT

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

BNC-F BULKHEAD RG316 RG174 GRIP

SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	SC6011	
SCALE	SHEET		