

MMCX-PLUG .086" SR DIRECT SOLDER R ANGLE

SC9537

SPECIFICATIONS

ELECTRICAL:




FREQUENCY: 0-6 GHZ
VSWR 1.25:1 MAX
IMPEDANCE: 50 OHMS
OP. TEMP RANGE: -55C to +125C

MECHANICAL:

MATERIAL BODY: BRASS AU PLATING
CENTER CONTACT: BRASS
CONTACT PLATING: Au MIL-G-45204
CAPTIVATED CONTACT
INSULATOR: TEFLON

ASSEMBLY

TRIM CABLE AS SHOWN,
INSERT CABLE INTO BODY,
SOLDER CONNECTOR BODY TO CABLE OUTER CONDUCTOR,
SOFT SOLDER CENTER CONTACT TO CABLE INNER CONDUCTOR,
INSERT INSULATOR
PRESS ON CAP



STRIPPING DIMENSIONS

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

MMCX-PLUG .086" SR DIRECT SOLDER R ANGLE

SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	SC9537	
SCALE		SHEET	