

MMCX-PLUG RG178 RA CRIMP

SC9541

SPECIFICATIONS

ELECTRICAL:


FREQUENCY: 0-6 GHZ
VSWR 1.25:1 MAX
IMPEDANCE: 50 OHMS
OP. TEMP RANGE: -55C to +125C

MECHANICAL:

MATERIAL BODY: BRASS AU PLATING
CENTER CONTACT: Brass
CONTACT PLATING: Au MIL-G-45204
CAPTIVATED CONTACT
INSULATOR: TEFLON

ASSEMBLY

TRIM CABLE AS SHOWN,
SLIDE CRIMP SLEEVE ON CABLE,
SLIDE CABLE INTO BODY UNTIL
IT RESTS IN CONTACT,
SLIDE CRIMP SLEEVE FORWARD, CRIMP,
SLIDE HEAT SHRINK INTO PLACE, SHRINK,
SOLDER CENTER CONDUCTOR,
PRESS CAP INTO BODY
CRIMP



STRIPPING DIMENSIONS

FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM				
TITLE MMCX-PLUG RG178 RA CRIMP				
SIZE A	CAGE CODE 3FKR5	DWG NO SC9541		REV
SCALE		SHEET		