

SMP/F-MCX/M FLEXIBLE CABLES 6GHZ SF086

SCA79086-XX

SPECIFICATIONS

CABLE ASSEMBLY:

VSWR:1.35:1 @<6GHZ TYPICAL

RAW CABLE: SF086

TYPICAL LOSS (EXCLUDING CONNECTORS)

@0.5GHz 0.15dB/ft

@1GHz 0.22dB/ft

@5GHz 0.5dB/ft

@10GHz 0.8dB/ft

@20GHz 1.3dB/ft

OUTER SHIELD DIAMETER: .087"

CONNECTORS:

SMA: Nickel PLATED BRASS


CONTACTS Au PLATING

INTERFACE: MIL-STD-348A

SMP(GPOtm COMPATIBLE)

Au PLATED BeCu

ROHS COMPLIANT



FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

SMP/F-MCX/M FLEXIBLE CABLES 6GHZ SF086

SIZE

A

CAGE CODE

3FKR5

DWG NO

SCA79086-XX

REV

--

ALL DIMENSIONS IN inches(MM) Typical

SCALE

SHEET