



N/F - N/F FLEXIBLE CABLES 1GHZ RG58DS

SCB11975-XX


SPECIFICATIONS

CABLE ASSEMBLY:
VSWR:1.2:1 @1GHZ TYPICAL


RAW CABLE: RG58DS
TYPICAL LOSS (EXCLUDING CONNECTORS)
@1GHz: 0.15 DB/FT
@2GHz: 0.22 DB/FT
@3GHz: 0.28 DB/FT

CONNECTORS: BRASS
CONTACTS Au PLATING
INTERFACE: MIL-STD-348A

OP TEMP: -55-110°C



MEASUREMENTS BELOW ARE TYPICAL



ALL DIMENSIONS IN inches(MM) Typical

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

N/F - N/F FLEXIBLE CABLES 1GHZ RG58DS

SIZE

A

CAGE CODE

3FKR5

DWG NO

SCB11975-XX

REV

--

SCALE

SHEET

