

SMA/M-SMA/MRA FLEXIBLE CABLES 1GHZ RG58CU

SCB15178-XX


SPECIFICATIONS

CABLE ASSEMBLY:
VSWR:1.2:1 @<1GHZ TYPICAL


RAW CABLE: RG58CU
TYPICAL LOSS (EXCLUDING CONNECTORS)
@1GHz: 0.15 DB/FT
@2GHz: 0.22 DB/FT
@3GHz: 0.28 DB/FT

CONNECTORS:
SMA: BRASS torque 5-in-lbs
CONTACTS: Au PLATING
INTERFACE: MIL-STD-348A

TEMPERATURE: -55° C to -110°C



MEASUREMENTS BELOW ARE TYPICAL



ALL DIMENSIONS IN inches(MM) Typical

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

SMA/M-SMA/MRA FLEXIBLE CABLES 1GHZ RG58CU

SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	SCB15178-XX	--
SCALE			SHEET