

SMA/M-SMA/F/BULKHEAD FLEXIBLE CABLE RG58CU

SCB15198-XX


SPECIFICATIONS

CABLE ASSEMBLY:
VSWR:1.2:1 @<6GHZ TYPICAL

RAW CABLE: RG58DS
TYPICAL LOSS (EXCLUDING CONNECTORS)
@1GHz: 0.15 DB/FT
@2GHz: 0.22 DB/FT
@3GHz: 0.28 DB/FT
@6GHz: 0.41 DB/FT

CONNECTORS:
BNC: BRASS
CONTACTS Au PLATING
INTERFACE: MIL-STD-348A

OP TEMP: -55 to +110°C
ROHS COMPLIANT



FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

SMA/M-SMA/F/BULKHEAD FLEXIBLE CABLE RG58CU

SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	SCB15198-XX	--
SCALE		SHEET	

ALL DIMENSIONS IN inches(MM) Typical