



SMA/M-N/M FLEXIBLE CABLES 1GHz RG58

SCB15223-XX


SPECIFICATIONS

CABLE ASSEMBLY:
VSWR:1.2:1 @< 1GHz TYPICAL


RAW CABLE: RG58
TYPICAL LOSS (EXCLUDING CONNECTORS)
@0.1GHz: 0.05 DB/FT
@0.5GHz: 0.11 DB/FT
@1GHz: 0.15 DB/FT

CONNECTORS:
BODY: BRASS
SMA-CONNECTOR TORQUE 5-in-lbs
CONTACTS Au PLATING
INTERFACE: MIL-STD-348A

TEMPERATURE: -55°C to +110°C



MEASUREMENTS BELOW ARE TYPICAL



ALL DIMENSIONS IN inches(MM) Typical

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

SMA/M-N/M FLEXIBLE CABLES 1GHz RG58

SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	SCB15223-XX	--
SCALE	SHEET		

