



BNC/M - N/M FLEXIBLE CABLES 1GHZ RG58

SCB15536-XX


SPECIFICATIONS

CABLE ASSEMBLY:
VSWR:1.2:1 @< 1GHZ TYPICAL


RAW CABLE: RG58
TYPICAL LOSS (EXCLUDING CONNECTORS)
@ 100MHZ: 0.05 DB/FT
@1GHZ: 0.15 DB/FT
@2GHZ: 0.22 DB/FT
@3GHZ: 0.28 DB/FT

CONNECTORS:
BNC: BRASS
CONTACTS Au PLATING
INTERFACE: MIL-STD-348A

OP TEMP: -55-110°C
ROHS COMPLIANT



MEASUREMENTS BELOW ARE TYPICAL



ALL DIMENSIONS IN inches(MM) Typical

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

BNC/M - N/M FLEXIBLE CABLES 1GHZ RG58

SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	SCB15536-XX	--
SCALE		SHEET	

