

SMA/M-SMA/F/BULKHEAD FLEXIBLE CABLE RG58AU

SCB15818-XX


SPECIFICATIONS

CABLE ASSEMBLY:
VSWR:1.2:1 @<1GHZ TYPICAL


RAW CABLE: RG58
TYPICAL LOSS (EXCLUDING CONNECTORS)
@1GHz: 0.15 DB/FT

CONNECTORS:
SMA: Ni PLATED BRASS
CONTACTS Au PLATING
INTERFACE: MIL-STD-348A
TORQUE: 5 in-LBS

TEMPERATURE: -55°C to -110°C



MEASUREMENTS BELOW ARE TYPICAL



ALL DIMENSIONS IN inches(MM) Typical

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

SMA/M-SMA/F/BULKHEAD FLEXIBLE CABLE RG58AU

SIZE

A

CAGE CODE

3FKR5

DWG NO

SCB15818-XX

REV

--

SCALE

SHEET