

# SCB15950-XX

## SPECIFICATIONS


CABLE ASSEMBLY:  
 VSWR: <1.2 TYPICAL @ 6 GHZ

RAW CABLE: (HAVERHILL HFLEX .086 OR EQ)  
 LOSS (EXCLUDING CONNECTORS)  
 @ 1GHZ: 0.15 DB/FT  
 @4GHZ: 0.33 DB/FT


OVERALL DIAMETER: .195"

CONNECTORS:  
 SMA: NICKEL PLATED BRASS  
 CONTACTS: Au PLATING  
 INTERFACE: MIL-STD-348A

TORQUE WRENCH; 5 IN-IBS



MEASUREMENTS BELOW ARE TYPICAL



ALL DIMENSIONS IN inches(MM) Typical

<b>FAIRVIEW MICROWAVE INC.</b>			
ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM			
TITLE			
<b>SMA FLEXIBLE CABLES RG58 6GHZ</b>			
SIZE	CAGE CODE	DWG NO	REV
<b>A</b>	3FKR5	<b>SCB15950-XX</b>	--
SCALE		SHEET	