

TNC/M-RA-TNC/M-RA FLEXIBLE CABLES 1GHZ RG58

SCB19295-XX


SPECIFICATIONS

CABLE ASSEMBLY:
VSWR:1.2:1 @1GHZ TYPICAL

RAW CABLE: RG58
TYPICAL LOSS (EXCLUDING CONNECTORS)
@1GHz: 0.15 DB/FT

CONNECTORS:
BNC: BRASS
CONTACTS Au PLATING
INTERFACE: MIL-STD-348A

OP TEMP: -55-110°C
ROHS COMPLIANT



FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

TNC/M-RA-TNC/M-RA FLEXIBLE CABLES
1GHZ RG58

SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	SCB19295-XX	--
SCALE		SHEET	

ALL DIMENSIONS IN inches(MM) Typical