



SMA/F/BLKH-D-MMCX/M FLEXIBLE CABLE RG174

SCB19928-XX


SPECIFICATIONS

CABLE ASSEMBLY:
VSWR:1.2:1 @< 3GHZ TYPICAL


RAW CABLE: RG174
TYPICAL LOSS (EXCLUDING CONNECTORS)
@0.1GHz 0.08 DB/FT
@0.5GHz 0.19 DB/FT
@1GHz 0.27 DB/FT
@2GHz 0.39 DB/FT
@3GHz 0.49 DB/FT

CONNECTORS: BRASS
SMA MATING torque 5-in-lbs
CONTACTS Au PLATING
INTERFACE: MIL-STD-348A

OP TEMP: -55-110°C
ROHS COMPLIANT



MEASUREMENTS BELOW ARE TYPICAL



ALL DIMENSIONS IN inches(MM) Typical

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

SMA/F/BLKH-D-MMCX/M FLEXIBLE CABLE RG174

SIZE

A

CAGE CODE

3FKR5

DWG NO

SCB19928-XX

REV

--

SCALE

SHEET

