



SMP/F-SMA/M/RA FLEXIBLE CABLES 12GHZ HF086

SCF43086-XX

SPECIFICATIONS


CABLE ASSEMBLY:
VSWR:1.35:1 @< 12GHZ TYPICAL

RAW CABLE: HARVERHILL HF086
TYPICAL LOSS (EXCLUDING CONNECTORS)
@1GHz: 0.23 DB/FT
@10GHz: 0.8 DB/FT
@18GHz: 1.1 DB/FT


CENTER CONDUCTOR DIAMETER: 0.0201"
OUTER SHIELD DIAMETER: .086"
OVERALL DIAMETER: 0.104"
SHIELD EFFECTIVENESS: -110dB

CONNECTORS:
SMA: Nickel PLATED BRASS
CONTACTS Au PLATING
INTERFACE: MIL-STD-348A
SMP(GPOtm COMPATIBLE)
Au PLATED BeCu

ROHS COMPLIANT



MEASUREMENTS BELOW ARE TYPICAL



ALL DIMENSIONS IN inches(MM) Typical

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

SMP/F-SMA/M/RA FLEXIBLE CABLES 12GHZ HF086

SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	SCF43086-XX	--
SCALE	SHEET		