




REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	ECO-16226	09/11/2026	HBAKKE	DWANG

7/16-28 UNEF-2A

4X ϕ .10 [2.6]

RECOMMENDED
MOUNTING HOLE

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS	
TOLERANCES:	
X = $\pm$.2 [5]	FRACTIONS $\pm$ 1/32
.XX = $\pm$.02 [0.5]	ANGLES $\pm$ 1°
.XXX = $\pm$.005 [0.13]	
CABLE LENGTH TOLERANCES:	
$\leq$ 12 [305] = +1 [25] / -0	
>12 [305] $\leq$ 60 [1524] = +2 [51] / -0	
>60 [1524] $\leq$ 120 [3048] = +4 [102] / -0	
>120 [3048] $\leq$ 300 [7620] = +6 [152] / -0	
>300 [7620] = +5% / -0	
CABLE LENGTH TOL IAW IPC A-620	
ALL DIMENSIONS ARE FOR REFERENCE ONLY AND SUBJECT TO CHANGE WITHOUT NOTICE UN-DIMENSIONED NON-CRITICAL FEATURES MAY VARY IN SIZE AND LOCATION COLORS MAY VARY	



Website: www.FairviewMicrowave.com
Phone: 1.800.715.4396 | 1.866.730.6243

INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5	
SCALE NONE	SHEET 1 OF 1

DESCRIPTION
TNC FEMALE (JACK) CONNECTOR STUB TERMINAL 4 HOLE
FLANGE (PANEL MOUNT), SOLDER

SIZE A	CAGE CODE 3FKR5	DRAWN BY HBAKKE	ITEM NO. SC4290	REV A
-----------	--------------------	--------------------	--------------------	----------