

SMA POWER DIVIDER RESISTIVE 2WAY 18 GHZ

MPR18-02

SPECIFICATIONS

ELECTRICAL:

RESISTIVE POWER DIVIDER

FREQUENCY: 0-18 GHZ

VSWR 1.35:1 MAX

POWER: 1 WATT CW, 1KW PEAK

INSERTION LOSS: 7.5 DB MAX

IMPEDANCE: 50 OHMS

AMPLITUDE TRACKING: 0.5DB

PHASE TRACKING: +/-2°


MATERIALS BODY: BRASS

CONNECTORS: STAINLESS STEEL

CONTACTS BeCU, Au PLATING MIL-G-45204

INTERFACE: MIL-STD-348B

TEMP: -55° TO +125° C



FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

SMA POWER DIVIDER RESISTIVE 2WAY 18 GHZ

SIZE CAGE CODE DWG NO

A

3FKR5

MPR18-02

REV

SCALE

SHEET